

SUPERIOR CODE READER FEATURES

WHOLE RACK READERS

Anti frost system which minimizes condensation of frozen samples (applies to, RD235 CRYO and DR505)

Scan time differs per scanner and varies from 1 to 5 seconds

High resolution image quality

Single tube reading option

Scans and decodes 2D Data-Matrix codes

Small benchtop solution

Compatible with most brands of sample storage tubes and racks

Compatible with 96-, 48-, and 24-well format racks

Supplied with Micronic Code Reader Software

SINGLE TUBE READERS

Unique condensation-free scanner plate

Produces unmatched data

Reads 1D rack barcodes 1D and 2D Data-Matrix coded tubes in less that 1 second

Easy to use - no software installation

Small footprint

Keyboard wedge functionality

Compatible with 96-, 48-, and 24-well rack and tube formats

OPTIONAL FEATURES

Micronic Side Barcode Readers

The Micronic Side Barcode Readers are available as an option for the following whole Rack Readers: the Tracxer Code Reader RD235 CRYO and the Micronic Rack Readers DR500, DR505 and DR700. When mounted, the Micronic Code Reader Software can read both the 1D rack barcode and 2D tube codes simultaneously.

CODE READER OVERVIEW & SPECIFICATIONS

Whole Rack Readers	Micronic Rack Reader DR700	Tracxer Code Reader RD235 CRYO	Micronic Rack Reader DR505	Micronic Rack Reader DR500
Basic Features Imaging technology Decode time Scan time Dimensions (mm) Decoding software	CCD 1 second 7 seconds 309 x 230 x 87 Micronic	CCD 1 second 7 seconds 298 x 180 x 66 Micronic	CIS 1 second 5 seconds 265 x 186 x 70 Micronic	CIS 1 second 5 seconds 265 x 186 x 70 Micronic
Software Compatibility Windows XP, 10, 8.1 and 7* Connection	Yes USB x2	Yes USB x2	Yes USB x2	Yes USB x2
Output Options Output text file Configure output file ODBC database push User account independent Network ready TCP/IP remote control	Yes Yes Yes Yes Yes Yes	Yes Yes Yes Yes Yes Yes	Yes Yes Yes Yes Yes Yes	Yes Yes Yes Yes Yes Yes
Tube/Rack Compatibility 24-well format tube/rack 48-well format tube/rack 96-well format tube/rack Read all 2D Data-Matrix codes	Yes Yes Yes Yes	Yes Yes Yes Yes	Yes Yes Yes Yes	Yes Yes Yes Yes
Other Features No tube, no code feature Single tube reading Rack templates Anti-frost system Robot gripper friendly Linear rack barcode reading Automatic code polarity recognition	Yes Yes Yes Yes Yes Optional Yes	Yes Yes Yes Yes Yes Optional No	Yes Yes Yes Yes Yes Optional Yes	Yes Yes Yes No Yes Optional Yes

* Please contact us for compatibility with other Windows versions.

www.micronic.com

© 2019 Micronic. All rights reserved. Specifications are subject to change. [PD811101]

Available in Canada from...

1-888-593-5969 • www.biolynx.ca • tech@biolynx.ca



BROCHURE

SERVING SCIENTISTS SINCE 1984

INDUSTRY LEADING 5-YEAR WARRANTY ON CODE READERS

ASSEMBLY IN THE NETHERLANDS AND THE UNITED STATES

MICRONIC CODE READER RANGE

Single Tube and Whole Rack Scanners

A COMPLETE RANGE FOR EVERY BUDGET

To enable fast, accurate and efficient sample identification, Micronic offers an extensive code reader range which consists of whole rack and single tube readers. The high-end DR700 and RD235 CRYO Rack Readers feature high resolution imaging technology for accurate 2D code reading, and an anti-frost system so that tube codes from even frozen samples can be read. The DR700 and RD235 CRYO have a scan time of approximately 7 seconds. To read 1D rack barcodes simultaneously, the Side Barcode Readers are available.

The Micronic Rack Reader DR500 and DR505 are small benchtop solutions that can read 2D codes quickly and cost effective within seconds. The compact readers are built for high throughput and automated systems. The DR505 version has an anti-frost system, which enables users to read racks filled with 2D codes tubes straight from the freezer. All Micronic Rack Readers are standard supplied with Micronic Code Reader Software to ensure an optimal performance.

To identify codes from single tubes, we offer easy to use single tube scanners. The versatile Tracxer Code Reader TS201 MINI can read 1D barcoded and 2D Data-Matrix coded tubes within 1 second. The Wireless Handheld Scanner MINI is a portable lightweight device.


MICRONIC CODE READER RANGE

SINGLE TUBE AND WHOLE RACK READERS

MICRONIC CODE READER SOFTWARE

The comprehensive Micronic Code Reader Software is fully compatible with all Micronic Rack Readers. The user friendly software is easy to use, gives reliable code readings and can be easily integrated into any laboratory sample database.

Developed on the basis of extensive user feedback, the new Micronic Code Reader Software features an automatic re-read function that ensures all the codes in a rack are deciphered quickly. After a rack is scanned, each cell contains a high-quality image of the code and tube ID, as well as a 'no tube, no code' feature if a tube cannot be found. Additional useful features include adjustment controls for brightness, contrast and threshold to optimize tube code display. Furthermore, the Micronic Code Reader Software features an automatic code polarity recognition function, which allows users to scan white on black code surfaces and black on white code surfaces, further improving compatibility. All features in the new software are included as standard at no extra cost with free upgrades and technical support.



IN-HOUSE ASSEMBLY & EXCEPTIONAL SERVICE

At Micronic, we develop and manufacture our premium labware and precision engineered equipment in-house. We are committed to offer top-of-the-line products, delivering exceptional quality, reliability and durability. Above all, we stand behind our solutions, and are confident that you will too.

Micronic Code Readers are assembled in the Netherlands and the United States. High-level service is of paramount importance at Micronic. Therefore, we have well-trained personnel on hand to provide service on equipment. These services range from annual maintenance, installation support and customization, to repairs.

Micronic warrants that its products are of satisfactory quality and conform to applicable EU legislation. If the product turns out to be defective, Micronic will arrange to repair or replace the product during the warranty period. The warranty period begins on the day the product was purchased from an authorized dealer and ends after 5 years for Micronic Reading equipment. In case of product replacement, the warranty start date remains the date of purchase of the original product. Micronic offers an industry leading warranty of 5 years, because we can!

5-Year
Warranty

Micronic Rack Reader DR700


Whole Rack Reader
MP35230



- Scan time is 7 seconds
- 309 x 230 x 87 mm
- CCD imaging technology
- 96, 48, 24-format compatible
- Anti-frost system
- Single tube reading
- Optional 1D Side Barcode Reader

Tracxer Code Reader RD235 CRYO

Whole Rack Reader
MP55122



- Scan time is 7 seconds
- 298 x 180 x 66 mm
- CCD imaging technology
- 96, 48, 24-format compatible
- Anti-frost system
- Single tube reading
- Optional 1D Side Barcode Reader

DID YOU KNOW...

The 2D Data-Matrix codes on Micronic sample storage tubes are permanently laser etched on the tube bottom so that they can never wear or fall off. Due to the optimal symbol contrast, modulation and print growth, and Micronic's 100% quality control on all 2D codes, the 2D codes can be easily read by scanners and readers. The 2D Data-Matrix codes are guaranteed unique and also have a human-readable code for secondary identification. The special custom 2D code service from Micronic enables customers to choose their own prefix of three digits which are followed by ten predefined digits which are also guaranteed unique.



Micronic Rack Reader DR505

Whole Rack Reader
MP35221



- Scan time is 5 seconds
- 254 x 157 x 47 mm
- CIS imaging technology
- 96, 48, 24-format compatible
- Anti-frost system
- Single tube reading
- Optional 1D Side Barcode Reader

Micronic Rack Reader DR500

Whole Rack Reader
MP35220



- Scan time is 5 seconds
- 254 x 157 x 47 mm
- CIS imaging technology
- 96, 48, 24-format compatible
- Single tube reading
- Optional 1D Side Barcode Reader

Micronic Side Barcode Reader for DR500 line

Side Barcode Reader
MP53240



- Scan time is 1 second
- 230 x 132 x 35 mm
- CCD imaging technology
- ANSI/SLAS barcoded rack compatible
- 1D Side Barcode Reader

Tracxer Code Reader TS201 MINI

Single Tube Reader
MP55126



- Scan time is 1 second
- 72 x 70 x 120 mm
- CIS imaging technology
- 96, 48, 24-format compatible
- 1D barcode reading
- 2D Data-Matrix code reading

Wireless Handheld Scanner MINI

Single Tube Reader
MP55127



- Scan time is 1 seconds
- 135 x 40 x 29 mm
- CIS imaging technology
- 96, 48, 24-format compatible
- 1D barcode reading
- 2D Data-Matrix code reading

DID YOU KNOW...

The Micronic Starter Packs are ideal for research laboratories that want to start using 2D coded tubes, or for those who are not satisfied with their current supplier and would like to try the high quality of Micronic products. Considering the amount of samples, the size of the lab and degree of automation, Micronic offers the Sample Storage Starter Packs in a range of formats: BASIC, STANDARD, ADVANCED, PREMIUM and PREMIUM+. All the Micronic Starter Packs contain 2D coded tubes with Screw or Push Caps, scanners, and manual or electric (de)capers. A Starter Pack saves up to 20%!

